

ULTRATECH

FCP160X50-Ø20

EAN 4031582445152



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Casting |
| Tread material | Ultratech Polyurethane, casted |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 6.3 in |
| Tread width | 1.97 in |
| Axle hole diameter | 0.79 in |
| Hub length | 2.36 in |
| Hardness of tread (A) | 92 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Ultratech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 1763.7 lb |
| Load capacity at 3.7 mph | 1410.96 lb |
| Load capacity Static | 3527.39 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 2.43 lb |

ULTRATECH

FCP160X50-Ø20

EAN 4031582445152



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

