

NOVATECH

ETY 060X20-Ø20 HL12

EAN 4031582318463
Broj porudžbine 00830217

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	100 kg
Nosivost na 6 km/h	80 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,14 kg

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj (RS/2RS)
Boja Tocak	Med žuta (RAL1005)
Prečnik	60 mm
Širina omotac	20 mm
dimenzija rupa osovin	20 mm
dužina glavcine	12 mm
Širina tela	20 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

NOVATECH

ETY 060X20-Ø20 HL12

EAN 4031582318463
Broj porudžbine 00830217



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

