

ALPHA SMART

3370DVR200P63

EAN 4031582331639
Order number 00035055



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Alpha smart
Type	Swivel castor
Load capacity at 1.8 mph	451.95 lb
Load capacity at 2.5 mph	451.95 lb
Load capacity Static	903.89 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	9.45 in
Overall weight	5.76 lb

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.18 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, heavy
Fork shape	Slim
Swivel bearing	Two ball races
Offset	2.07 in
Swivel radius	6 in
Swivel interference	12.01 in

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	3.03 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

ALPHA SMART

3370DVR200P63

EAN 4031582331639
Order number 00035055



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

