PRODUCT INFORMATION

DURATECH HEAT

BOG100x35-Ø11

EAN 4031582428377

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Diameter	3.94 in
Tread width	1.38 in
Axle hole diameter	0.44 in
Hub length	1.71 in
Hardness of tread (D)	85 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●●
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	275.58 lb
Electric conductive	no
Stainless	no
Load capacity Static	551.16 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall weight	0.56 lb

© Copyright 2026 TENTE International GmbH


DURATECH HEAT

BOG100x35-Ø11

EAN 4031582428377

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH