

# LINEA

5940XSP125R05-22 RAL9002

EAN 4031582352009



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Linea                     |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 130 kg                    |
| Electric conductive         | ✓                         |
| Load capacity Static        | 260 kg                    |
| Temperature range (Minimum) | -10 °C                    |
| Temperature range (Maximum) | 40 °C                     |
| Overall height              | 145 mm                    |
| Overall width               | 82 mm                     |
| Overall weight              | 0.96 kg                   |

## WHEEL

|                       |                                             |
|-----------------------|---------------------------------------------|
| Body material         | Polyamide, electric conductive              |
| Tread material        | Polyurethane, injected, electric-conductive |
| Bearing               | Precision ball bearing                      |
| Threadguards          | With threadguard                            |
| Diameter              | 125 mm                                      |
| Tread width           | 20 mm                                       |
| Hardness of tread (A) | 92 Shore A                                  |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material fork       | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel bearing      | Precision ball bearing |
| Offset              | 40 mm                  |
| Swivel radius       | 109 mm                 |
| Swivel interference | 218 mm                 |
| Dome diameter       | 52 mm                  |

## FITTING

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 22 mm             |
| Bolt length   | 40 mm             |



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award

# LINEA

5940XSP125R05-22 RAL9002

EAN 4031582352009



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

