

# DURATECH

TOP 082X80-Ø20 HL82

EAN 4031582322606  
Order number 00802945



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	82 mm
Tread width	80 mm
Axle hole diameter	20 mm
Hub length	82 mm
Body width	80 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	750 kg
Load capacity at 6 km/h	600 kg
Load capacity Static	1500 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.506 kg

# DURATECH

TOP 082X80-Ø20 HL82

EAN 4031582322606  
Order number 00802945



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

