

LUMINA

A520POI040L51-8



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel caster
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	22.05 lb
Electric conductive	no
Stainless	no
Load capacity Static	44.09 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	1.73 in
Overall width	1.5 in
Overall weight	0.05 lb

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Swivel radius	1.42 in
Swivel interference	2.83 in

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.57 in
Tread width	0.31 in
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.31 in

LUMINA

A520POI040L51-8



BETTER MOBILITY. BETTER LIFE.

Product Drawings

