

ELASTECH

UER100X34-Ø12 HL44,4

EAN 4031582442854



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.54 lb

WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.34 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Hardness of tread (A)	64 Shore A

ELASTECH

UER100X34-Ø12 HL44,4

EAN 4031582442854



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

