PRODUCT INFORMATION

AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



Image may differ from the original product

CORE ATTRIBUTES

Product Name	Agila twin
Type	Swivel castor with total lock
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Overall Height	99 mm

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel Bearing	Two ball races
Offset	31 mm
Swivel interference	198 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	10 mm


AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH