

# DURATECH HEAT

BOG080X35-Ø8 HL45,5 (CASQUILLO ZINC)

EAN 4031582416459



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Duratech heat                 |
| Housing type                | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 220.46 lb                     |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | -40 °F                        |
| Temperature range (Maximum) | 536 °F                        |
| Overall weight              | 0.46 lb                       |

## WHEEL

|                       |                                   |
|-----------------------|-----------------------------------|
| Body material         | Plastic thermoset, heat-resistant |
| Tread material        | Identical with wheel body         |
| Bearing               | Dry bearing bush                  |
| Diameter              | 3.15 in                           |
| Tread width           | 1.38 in                           |
| Axle hole diameter    | 0.31 in                           |
| Hub length            | 1.77 in                           |
| Hardness of tread (D) | 85 Shore D                        |

# DURATECH HEAT

BOG080X35-Ø8 HL45,5 (CASQUILLO ZINC)

EAN 4031582416459



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

