

# PLATE

P10-40x27 / 8

EAN 4031582320152



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Corrosion resistance | ● ● ● ○ ○ |
|----------------------|-----------|

## CORE ATTRIBUTES

|                          |                |
|--------------------------|----------------|
| Product name             | Mounting plate |
| Type                     | Accessory      |
| Load capacity at 1.8 mph | 88.18 lb       |
| Electric conductive      | no             |
| Stainless                | no             |
| Load capacity Static     | 176.37 lb      |
| Overall height           | 0.31 in        |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Stem with U-shaped plate |
| Plate length                | 1.57 in                  |
| Plate width                 | 1.06 in                  |
| Plate hole length (Maximum) | 1.26 in                  |
| Plate hole width (Maximum)  | 1.26 in                  |
| Plate hole diameter         | 0.16 in                  |