

ALPHA

3478IEP100P63 CL50 OH125

EAN 4031582306392
Order number 00030864



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	125 mm
Overall width	115 mm
Overall weight	0.989 kg

WHEEL

Body material	Aluminium
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	100 mm
Tread width	40 mm
Body width	40 mm
Hardness of tread (A)	68 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Colour	Blue passivated

FITTING

Fitting type	Medium rectangular plate
Plate length	136 mm
Plate width	117 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ALPHA

3478IEP100P63 CL50 OH125

EAN 4031582306392
Order number 00030864



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

