

DURATECH HEAT

W00075X25-Ø8 HL26,5

EAN 4031582367355



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech heat
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	200 °C

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Axle hole diameter	8 mm
Hub length	26.5 mm

DURATECH HEAT

W00075X25-Ø8 HL26,5

EAN 4031582367355



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

