

# NOVATECH

ETP 082x70-Ø20 HL70

EAN 4031582318715



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Steel, iron            |
| Tread Material Mix    | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Wheel Color           | Honey yellow (RAL1005) |
| Threadguards          | With threadguard       |
| Diameter              | 82 mm                  |
| Tread width           | 70 mm                  |
| Axle Hole Diameter    | 20 mm                  |
| Hub Length            | 70 mm                  |
| Body width            | 70 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |
| Bearing type          | 6204                   |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Novatech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 700 kg                        |
| Load capacity at 6 km/h     | 840 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 1400 kg                       |
| Temperature range (Minimum) | -10 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 0.95 kg                       |

