

PURETECH AIR

DQR260X85-Ø25 HL74 4PR

EAN 4031582318111



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik lista
	mekan
materijal omotaca	Pneumatička guma, profil bloka
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	260 mm
Širina omotac	85 mm
dimenzija rupa osovina	25 mm
dužina glavcine	74 mm
Teškoća gazećeg omotac (A)	55 Šor A

PERFORMANSE

Performanse kotrljanja ● ○ ○ ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda Puretech air

Tip Tocak

Nosivost na 3 km/h 150 kg

Statički Nosivost 300 kg

Ukupna težina 1,35 kg

PURETECH AIR

DQR260X85-Ø25 HL74 4PR

EAN 4031582318111



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

