

STYLEA

5920UOI035L51-10 LH 9011/9011

EAN 4031582356731



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Stylea
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	33 mm
Overall width	52 mm
Overall weight	0.05 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	12 mm
Swivel radius	37 mm
Swivel interference	74 mm
Dome diameter	15.2 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	35 mm
Tread width	12 mm
Body width	12 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

STYLEA

5920UOI035L51-10 LH 9011/9011

EAN 4031582356731

Order number 00078712
Product Drawings



BETTER MOBILITY. BETTER LIFE.

