

DURATECH

TOP 085x65-Ø20 HL65

EAN 4031582331172



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	650 kg
Nosivost na 6 km/h	520 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1300 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0.54 kg

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	85 mm
Širina omotac	65 mm
dimenzija rupa osovina	20 mm
dužina glavcine	65 mm
Širina tela	65 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204

