PRODUCT INFORMATION

OMIKRON TWIN

9958FTP400P68

EAN 4031582317022




Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Omikron twin
Type	Fixed castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 4 km/h	7200 kg
Load capacity at 6 km/h	5000 kg
Electric Conductive	No
Stainless	No
Load capacity Static	10800 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall Height	510 mm
Overall width	285 mm
Overall weight	71.44 kg

HOUSING

Housing Material	Iron forged, heavy
Fork shape	Twin wheel housing
Housing Color	Transparent coating
Lubrication nipple	1
Dome diameter	235 mm

WHEEL

Body material	Cast iron
Tread Material Mix	PUR casted premium
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	400 mm
Tread width	80 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Extra large rectangular heavy-duty plate
Plate length	270 mm
Plate width	250 mm
Plate hole length (Maximum)	210 mm
Plate hole width (Maximum)	230 mm
Plate hole diameter	17 mm

© Copyright 2026 TENTE International GmbH


OMIKRON TWIN


9958FTP400P68


EAN 4031582317022

Order number 00801592

Product Drawings







© Copyright 2026 TENTE International GmbH