PRODUCT INFORMATION

# OMIKRON TWIN

## 9958FTP400P68

EAN 4031582317022




Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion Resistance | ●●●●○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Omikron twin |
| Type | Fixed castor |
| Standard | similar EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 7200 kg |
| Load capacity at 6 km/h | 5000 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 10800 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 510 mm |
| Overall width | 285 mm |
| Overall weight | 71.44 kg |

### HOUSING

| | |
|---|---|
| Housing Material | Iron forged, heavy |
| Fork shape | Twin wheel housing |
| Housing Color | Transparent coating |
| Lubrication nipple | 1 |
| Dome diameter | 235 mm |

### WHEEL

| | |
|---|---|
| Body material | Cast iron |
| Tread Material Mix | PUR casted premium |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel Color | Honey yellow (RAL1005) |
| Threadguards | With threadguard |
| Diameter | 400 mm |
| Tread width | 80 mm |
| Body width | 80 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

### FITTING

| | |
|---|---|
| Fitting type | Extra large rectangular heavy-duty plate |
| Plate length | 270 mm |
| Plate width | 250 mm |
| Plate hole length (Maximum) | 210 mm |
| Plate hole width (Maximum) | 230 mm |
| Plate hole diameter | 17 mm |

© Copyright 2026 TENTE International GmbH


# OMIKRON TWIN


9958FTP400P68


EAN 4031582317022

Order number 00801592

**Product Drawings**




© Copyright 2026 TENTE International GmbH