

ALPHA

3478DIJ200P63

EAN 4031582306255
Order number 00030041



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	451.95 lb
Load capacity Static	903.89 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	9.45 in
Overall weight	6.55 lb

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in
Hardness of tread (A)	80 Shore A

HOUSING

Material	Steel sheet, heavy
Fork shape	Broad

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.53 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

ALPHA

3478DIJ200P63

EAN 4031582306255
Order number 00030041



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

