

PRODUCT INFORMATION

NOVATECH

ITP 150x50-Ø20 HL60

EAN 4031582319897



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Body material	Aluminium
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Wheel Color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	150 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ● ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	650 kg
Load capacity at 6 km/h	520 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1300 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.18 kg




PRODUCT INFORMATION

NOVATECH

ITP 150x50-020 HL60

EAN 4031582319997

Order number 00829121



BETTER MOBILITY. BETTER LIFE.