PRODUCT INFORMATION

LINEA LIGHT

5925POH065L51-10

EAN 4031582404005

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Linea light
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	68 mm
Overall width	46 mm
Overall weight	0.09 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Swivel radius	67 mm
Swivel interference	134 mm
Dome diameter	23 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	65 mm
Tread width	13.9 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH


LINEA LIGHT


5925POH065L51-10

EAN 4031582404005

TENTE
BETTER MOBILITY. BETTER LIFE.

Product Drawings





Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH