

DURATECH

MOP 250x80-Ø50 HL90

EAN 4031582320084



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	250 mm
Širina omotac	80 mm
dimenzija rupa osovina	50 mm
dužina glavnice	90 mm
Širina tela	80 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6310

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	6600 kg
Nosivost na 6 km/h	5500 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	11000 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	6.2 kg

DURATECH


MOP 250x80-Ø50 HL90

EAN 4031582320084

Broj porudžbine 00830850
Product Drawings



BETTER MOBILITY. BETTER LIFE.




DURATECH

MOP 250x80-Ø50 HL90

EAN 4031582320084

Broj porudžbine 40836850



BETTER MOBILITY. BETTER LIFE.