

# AGILA

2475DYK050P30-11

EAN 4031582344318  
Order number 00005489



Image may differ from the original product

### PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

### CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Agila                          |
| Housing type                | Swivel castor with wheel brake |
| Standard                    | EN12530 - Devices Castors      |
| Load capacity at 3 km/h     | 40 kg                          |
| Electric conductive         | ✓                              |
| Load capacity Static        | 80 kg                          |
| Temperature range (Minimum) | -20 °C                         |
| Temperature range (Maximum) | 85 °C                          |
| Overall height              | 69 mm                          |
| Overall width               | 43 mm                          |
| Overall weight              | 0.222 kg                       |

### WHEEL

|                       |                                          |
|-----------------------|------------------------------------------|
| Body material         | Sheet Steel                              |
| Tread material        | Solid rubber, black, electric-conductive |
| Bearing               | Cone ball bearing                        |
| Wheel color           | Blue passivated                          |
| Threadguards          | With threadguard                         |
| Diameter              | 50 mm                                    |
| Tread width           | 19 mm                                    |
| Body width            | 19 mm                                    |
| Hardness of tread (A) | 80 Shore A                               |

### HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Colour              | Blue passivated     |
| Offset              | 24 mm               |
| Swivel radius       | 82 mm               |
| Swivel interference | 164 mm              |
| Dome diameter       | 41 mm               |

### FITTING

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| Fitting type       | Bolt hole                                                  |
| Bolt hole diameter | 11 mm                                                      |
| Hint               | Castors can be mounted with standard screws of any length. |

# AGILA

2475DYK050P30-11

EAN 4031582344318  
Order number 00005489



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

