

PRODUCT INFORMATION

MAXTECH EVO

PBO200x48-Ø12 HL35 TFR

EAN 4031582400380



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech evo
Type	Wheel
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Overall weight	0.77 lb

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, biosourced, injected
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.89 in
Axle hole diameter	0.47 in
Hub length	1.34 in

MAXTECH EVO

PBO200x48-Ø12 HL35 TFR

EAN 4031582400380



BETTER MOBILITY. BETTER LIFE.

Product Drawings

