

AGILA US

2670PJO4X1.25P30-13

EAN 4031582434767



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance ● ● ● ○ ○

Movement noise ● ● ○ ○ ○

Attrition ● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila US
Housing type	Swivel castor
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 1.8 mph	249.12 lb
Load capacity Static	498.24 lb
Overall height	5 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	4 in
Tread width	1.25 in
Axle hole diameter	0.39 in
Hub length	1.61 in
Hardness of tread (A)	77 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Offset	1.5 in
Swivel radius	3.5 in
Swivel interference	6.93 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in