PRODUCT INFORMATION

# LINEA

## 5947XSC125P30-13 RAL9002

EAN 4031582352580

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●● |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion Resistance | ●●●●○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Linea |
| Type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 130 kg |
| Electric Conductive | Yes |
| Stainless | Yes |
| Load capacity Static | 260 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall Height | 143 mm |
| Overall width | 82 mm |
| Overall weight | 0.87 kg |

### HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel Bearing | Precision ball bearing |
| Housing Color | Grey white (RAL9002) |
| Offset | 40 mm |
| Swivel radius | 129 mm |
| Swivel interference | 258 mm |
| Dome diameter | 52 mm |

### WHEEL

| | |
|---|---|
| Body material | Polyamide, electric conductive |
| Tread Material Mix | Polyurethane, injected, electric-conductive |
| Bearing | Precision ball bearing, stainless |
| Threadguards | With threadguard |
| Diameter | 125 mm |
| Tread width | 20 mm |
| Hardness of tread (A) | 92 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Bolt hole |
| Bolt hole diameter | 13 mm |

Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH


# LINEA

5947XSC125P30-13 RAL9002

EAN 4031582352580

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH