PRODUCT INFORMATION

ELASTECH

SFP 200x50-Ø20 HL60 plus

EAN 4031582322217



Image may differ from the original product

PERFORMANCE

Roll Performance	●●○○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1322.77 lb
Load capacity at 3.7 mph	1102.31 lb
Electric conductive	no
Stainless	no
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	7.67 lb

WHEEL

Tread hardness	soft
Body material	Sheet steel, heavy
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Wheel color	Gray / non- marking
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	68 Shore A

© Copyright 2026 TENTE International GmbH


ELASTECH

SFP 200x50-Ø20 HL60 plus

EAN 4031582322217

Order number 00830559

Product Drawings




© Copyright 2026 TENTE International GmbH

ELASTECH

SFP 200x50-Ø20 HL60 plus

EAN 4031582322217

Order number 00830959



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH