

PRODUCT INFORMATION

PURETECH

PVO250x50-Ø20,1 HL58 TRG

EAN 4031582404265



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Puretech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 396.83 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 793.66 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 4.49 lb                       |



BETTER MOBILITY. BETTER LIFE.

WHEEL

|                       |                     |
|-----------------------|---------------------|
| Body material         | Polypropylene       |
| Tread material        | Solid rubber, black |
| Bearing               | Plain bearing       |
| Threadguards          | Without threadguard |
| Diameter              | 9.84 in             |
| Tread width           | 1.97 in             |
| Axle hole diameter    | 0.79 in             |
| Hub length            | 2.28 in             |
| Hardness of tread (A) | 85 Shore A          |

# PURETECH

PVO250x50-Ø20,1 HL58 TRG

EAN 4031582404265



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

