

FOOTMASTER

FOOT MASTER GATD-150-ASF-HUD

EAN 4031582495256
Order number 00800114



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	630 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall height	200 mm
Overall width	155 mm
Overall weight	14.68 kg

WHEEL

Bearing	Unmachined hub
Diameter	150 mm
Tread width	40 mm
Body width	40 mm

HOUSING

Offset	35 mm
Swivel radius	123 mm
Swivel interference	246 mm
Dome diameter	130 mm

FITTING

Plate length	145 mm
Plate width	145 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	11 mm

FOOTMASTER

FOOT MASTER GATD-150-ASF-HUD

EAN 4031582495256
Order number 00800114



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

