

# SUPRATECH

PJO4X1.25-Ø0.5 HL40

EAN 4031582436068



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | Without threadguard  |
| Diameter              | 101.6 mm             |
| Tread width           | 31.75 mm             |
| Axle hole diameter    | 12.1 mm              |
| Hub length            | 40 mm                |
| Hardness of tread (A) | 77 Shore A           |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                         |  |
|-------------------------|--|
| Product name            | Supratech                                    |
| Housing type            | Wheel  |
| Standard                | Institute of Casters and Wheel Manufacturers |
| Load capacity at 3 km/h | 113 kg                                       |
| Load capacity Static    | 226 kg                                       |

# SUPRATECH

PJO4X1.25-Ø0.5 HL40

EAN 4031582436068



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

