

# STORA

2340PHP125P30-13

EAN 4031582357646



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Stora
Type	Swivel castor
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	6.18 in

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber, antistatic
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.26 in
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Precision ball bearing
Offset	1.5 in
Swivel radius	3.96 in
Swivel interference	7.91 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

# STORA

2340PHP125P30-13

EAN 4031582357646



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

