

FOOTMASTER

FOOT MASTER GD- 40-S-NYN

EAN 4031582413199



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	60 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	60 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	71 mm
Ukupna širina	58 mm
Ukupna težina	0.32 kg

KUCISTE

Boja	Beli
ofset	30 mm
okretni radijus	51 mm
Otpor okretanju	102 mm
Prečnik kupole	58 mm

TOCAK

Nošenje	kotrljajuci lezaj, navlažen
Boja Tocak	Crna
Prečnik	42 mm
Širina omotac	19 mm
Širina tela	19 mm

FOOTMASTER

FOOT MASTER GD- 40-S-NYN

EAN 4031582413199

Broj porudžbine 00062067
Product Drawings



BETTER MOBILITY. BETTER LIFE.

