

MAXTECH

PNP 200X50-Ø8 HL60

EAN 4031582320657
Order number 00005570



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Wheel color	Black
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	8 mm
Hub length	60 mm
Body width	50 mm
Hardness of tread (A)	70 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.66 kg

PRODUCT INFORMATION

MAXTECH

PNP 200X50-Ø8 HL60

EAN 4031582320657
Order number 00005570



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

