

# PLATE

P11-40x25 / 8

EAN 4031582320206



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Stem with L-shaped plate
Plate length	40 mm
Plate width	25 mm
Plate hole length (Maximum)	32 mm
Plate hole width (Maximum)	32 mm
Plate hole diameter	4 mm

## PERFORMANCE

Corrosion Resistance ●●●○○

## CORE ATTRIBUTES

Product Name	Plate
Type	Accessory
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Overall Height	8 mm