

# PLATE

P11-40x25 / 8

EAN 4031582320206



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Corrosion Resistance ●●●○○

## CORE ATTRIBUTES

|                         |           |
|-------------------------|-----------|
| Product Name            | Plate     |
| Type                    | Accessory |
| Load capacity at 3 km/h | 40 kg     |
| Electric Conductive     | No        |
| Stainless               | No        |
| Load capacity Static    | 80 kg     |
| Overall Height          | 8 mm      |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Stem with L-shaped plate |
| Plate length                | 40 mm                    |
| Plate width                 | 25 mm                    |
| Plate hole length (Maximum) | 32 mm                    |
| Plate hole width (Maximum)  | 32 mm                    |
| Plate hole diameter         | 4 mm                     |