

B40 - 11X20 / 10

EAN 4031582418002



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 1.8 mph	132.28 lb
Load capacity Static	264.55 lb
Overall height	0.18 in
Overall weight	0.08 lb

FITTING

Fitting type	Stem with synthetic circlip, with collar
Stem diameter	0.43 in