

ALPHA

3478UFP125P62

EAN 4031582327649
Order number 00026480



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha |
| Type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 250 kg |
| Load capacity Static | 500 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 155 mm |
| Overall width | 85 mm |
| Overall weight | 0.831 kg |

WHEEL

| | |
|-----------------------|---------------------------------------|
| Body material | Polyamide |
| Tread hardness | soft |
| Tread material | Elastic tire, non-marking, vulcanized |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 125 mm |
| Tread width | 40 mm |
| Body width | 40 mm |
| Hardness of tread (A) | 63 Shore A |

HOUSING

| | |
|---------------|--------------------|
| Material fork | Steel sheet, heavy |
| Fork shape | Broad |
| Colour | Blue passivated |

FITTING

| | |
|-----------------------------|-------------------------|
| Fitting type | Small rectangular plate |
| Plate length | 103 mm |
| Plate width | 85 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 60 mm |
| Plate hole width (Minimum) | 77 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 9 mm |

ALPHA

3478UFP125P62

EAN 4031582327649
Order number 00026480



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

Technical drawing of a wheel assembly (part 12) showing front, side, and top views with dimensions. The front view shows a diameter of $\varnothing 125 \pm 0,2$. The side view shows a height of 85.57 and a width of 46.51. The top view shows a width of 80.45/77.45 and a height of 86.51. A 3D perspective view of the wheel is shown to the right.

Achtung! Zeichnungsänderungen nur nach Freigabe!
attention! amendment of drawing only after release!

Notice the protective note 100 14019.

The reproduction, distribution and utilization of this drawing as well as the communication of this content to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.

Schutzmerkmal 100 14019 beachten.
Weitergabe sowie Vervielfältigung dieser Zeichnung, Verbreitung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
Zusammenfassungen sind außerdem zu Schadenersatz.
Alle Rechte für den Fall der Patente, Gebrauchsmuster oder Geschmackschutzverordnungen vorbehalten.

| | | | |
|--------------|------------|------------------|--|
| Abgesehen | Überfläche | Reaktion: 10, 12 | mit Holz Folie versehen |
| | | Material: | <input type="checkbox"/> Folie <input type="checkbox"/> Holz Folie <input type="checkbox"/> Holz |
| | | 3478 125P62 | |
| TENTE | | TR11457 | 1001 |
| City | Address | Street | Zip Code |
| | | | |