

PRODUCT INFORMATION

DURATECH HEAT

WOO080x31 Ø12 TFR

EAN 4031582393842



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	440.92 lb
Electric conductive	no
Stainless	no
Load capacity Static	881.85 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	356 °F
Overall weight	0.17 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.22 in
Axle hole diameter	0.47 in
Hub length	1.57 in
Hardness of tread (D)	75 Shore D

DURATECH HEAT

WOO080x31 Ø12 TFR

EAN 4031582393842



BETTER MOBILITY. BETTER LIFE.

Product Drawings

