

# DURATECH HEAT

W00080X31 Ø12 TFR

EAN 4031582393842



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |  |
|-----------------------|--|
| Body material         | Thermoplastic synthetics, heat resistant |
| Tread material        | Identical with wheel body                |
| Bearing               | Plain bearing                            |
| Threadguards          | Without threadguard                      |
| Diameter              | 80 mm                                    |
| Tread width           | 31 mm                                    |
| Axle hole diameter    | 12 mm                                    |
| Hub length            | 40 mm                                    |
| Hardness of tread (D) | 75 Shore D                               |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Duratech heat                 |
| Housing type                | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 200 kg                        |
| Load capacity Static        | 400 kg                        |
| Temperature range (Minimum) | -40 °C                        |
| Temperature range (Maximum) | 180 °C                        |
| Overall weight              | 0.078 kg                      |

# DURATECH HEAT

W00080X31 Ø12 TFR

EAN 4031582393842



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

