

# ALPHA

3470DYJ100P62

EAN 4031582412000



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha                         |
| Housing type                | Swivel castor                 |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 154.32 lb                     |
| Load capacity Static        | 308.65 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 5.04 in                       |
| Overall weight              | 2.02 lb                       |

## WHEEL

|                       |                                          |
|-----------------------|------------------------------------------|
| Body material         | Sheet Steel                              |
| Tread material        | Solid rubber, black, electric-conductive |
| Bearing               | Roller bearing                           |
| Axle                  | Screwed with nut                         |
| Threadguards          | With threadguard                         |
| Diameter              | 3.94 in                                  |
| Tread width           | 1.18 in                                  |
| Hardness of tread (A) | 85 Shore A                               |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material            | Steel sheet, heavy |
| Fork shape          | Broad              |
| Swivel bearing      | Two ball races     |
| Offset              | 1.57 in            |
| Swivel radius       | 3.54 in            |
| Swivel interference | 7.09 in            |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 4.13 in           |
| Plate width                 | 3.15 in           |
| Plate hole length (Minimum) | 3.03 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Maximum)  | 2.36 in           |
| Plate hole diameter         | 0.35 in           |

# ALPHA

3470DYJ100P62


EAN 4031582412000



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

3470U00100P62-neu



Platte 3470-080P62-105x80

