PRODUCT INFORMATION

DURATECH

UOR 100x36-Ø12 HL44,4

EAN 4031582323535

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Roller bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	100 mm
Tread width	36 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Body width	36 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Electric Conductive	No
Stainless	No
Load capacity Static	400 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.18 kg

© Copyright 2026 TENTE International GmbH


DURATECH

UOR 100x36-Ø12 HL44,4

EAN 4031582323535

Order number 00030965

Product Drawings



© Copyright 2026 TENTE International GmbH