

PRODUCT INFORMATION

# DURATECH

TOP 080X74-Ø20 HL80

EAN 4031582331028  
Order number 00829536



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	2.91 in
Axle hole diameter	0.79 in
Hub length	3.15 in
Body width	2.91 in
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1543.23 lb
Load capacity at 3.7 mph	1234.59 lb
Load capacity Static	3086.47 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.99 lb

# DURATECH

TOP 080X74-Ø20 HL80

EAN 4031582331028  
Order number 00829536



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

