PRODUCT INFORMATION

DURATECH SILENT

HUR125x36-Ø12 HL44

EAN 4031582452884



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●●
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech silent
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Electric Conductive	No
Stainless	No
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.61 kg

WHEEL

Body material	Damping, hybrid material
Tread Material Mix	Polyamide
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	36 mm
Axle Hole Diameter	12 mm
Hub Length	44 mm
Hardness of tread (D)	75 Shore D

© Copyright 2026 TENTE International GmbH


DURATECH SILENT

HUR125x36-Ø12 HL44

EAN 4031582452884

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH