

COMPACTA

1430PJI025P60-35X30

EAN 4031582415056



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	86 mm
Overall width	24 mm
Overall weight	0.03 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	25 mm
Tread width	15 mm
Body width	15 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	One ball race
Colour	Blue passivated
Offset	23 mm
Swivel radius	82 mm
Swivel interference	164 mm
Dome diameter	24.5 mm
Thread diameter	0 mm

FITTING

Fitting type	Rectangular plate
Plate length	35 mm
Plate width	30 mm
Plate hole length (Maximum)	23 mm
Plate hole width (Maximum)	28 mm
Plate hole diameter	4.2 mm
Stem length	15 mm

PRODUCT INFORMATION

COMPACTA

1430PJI025P60-35X30

EAN 4031582415056



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

