

NOVATECH

FTP 125X50-Ø25 HL60

EAN 4031582330694
Order number 00833771



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	125 mm
Tread width	50 mm
Axle hole diameter	25 mm
Hub length	60 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	660 kg
Load capacity at 6 km/h	550 kg
Load capacity Static	1100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	2.405 kg

NOVATECH

FTP 125X50-Ø25 HL60

EAN 4031582330694
Order number 00833771



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

