

PURETECH

PVR 200X50-Ø25

EAN 4031582321319

Broj porudžbine 00050597



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
stitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavčine	58 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●●○

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	205 kg
Statički Nosivost	410 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1,17 kg

PURETECH

PVR 200X50-Ø25

EAN 4031582321319

Broj porudžbine 00050597



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

