PRODUCT INFORMATION

AGILA TWIN

2976PJH075P54 offset-28 no-Cr-VI

EAN 4031582302875




Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●●○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel caster with central , total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	4.06 in
Overall width	2.8 in
Overall weight	1.28 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Housing Color	Yellow passivated
Offset	1.1 in
Swivel radius	2.58 in
Swivel interference	5.16 in
Dome diameter	2.56 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Slate gray (RAL7015)
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate with brake elements
Plate length	2.76 in
Plate width	2.17 in
Plate hole length (Minimum)	2.01 in
Plate hole length (Maximum)	1.61 in
Plate hole width (Minimum)	2.01 in
Plate hole width (Maximum)	2.24 in
Plate hole diameter	0.22 in

© Copyright 2026 TENTE International GmbH


AGILA TWIN


2976PJH075P54 offset-28 no-Cr-VI


EAN 4031582302875


Order number 00028313

Product Drawings









© Copyright 2026 TENTE International GmbH