

PURETECH AIR

PQR260X85-Ø25 HL74 2PR

EAN 4031582321081
Order number 00031045



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Pneumatic tire, block profile
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	10.24 in
Tread width	3.35 in
Axle hole diameter	0.98 in
Hub length	2.91 in
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Housing type	Wheel
Load capacity at 1.8 mph	330.69 lb
Load capacity Static	330.69 lb
Overall weight	2.29 lb

PRODUCT INFORMATION

PURETECH AIR

PQR260X85-Ø25 HL74 2PR

EAN 4031582321081
Order number 00031045



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

