

PRODUCT INFORMATION

SUPRATECH

PJI050x19-Ø8 NEGRA

EAN 4031582457285



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Supratech                 |
| Type                        | Wheel                     |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 40 kg                     |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 80 kg                     |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall weight              | 0.02 kg                   |

WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread Material Mix    | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Threadguards          | Without threadguard            |
| Diameter              | 50 mm                          |
| Tread width           | 19 mm                          |
| Axle Hole Diameter    | 6 mm                           |
| Hub Length            | 21.5 mm                        |
| Hardness of tread (A) | 87 Shore A                     |

# SUPRATECH

PJI050x19-Ø8 NEGRA

EAN 4031582457285



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

